

Cascadetabel: installatieautomaten smeltveiligheden

| | Automatenserie | | NB | NC | ND | HM | Diazed | | NH GL | |
|--------------|-------------------|-------|------|------|------|------|--------|-------|---------|----------|
| | Afschakelvermogen | | 10kA | 10kA | 10kA | 15kA | Snel | Traag | | |
| IEC60898-1 | Karakteristiek | | B | C | D | C | 100A | 80A | 20-100A | 125-160A |
| MH | 4,5 kA | B | 10kA | 10kA | 10kA | 10kA | - | - | 40kA | 20kA |
| MJ | 4,5 kA | C | 10kA | 10kA | 10kA | 10kA | - | - | 40kA | 20kA |
| AD | 6 kA | B - C | 6kA | 6kA | 6kA | 6kA | - | - | - | - |
| MB/MK | 6 kA | B | 10kA | 10kA | 10kA | 10kA | 50kA | 50kA | 50kA | 25kA |
| MC | 6 kA | C | 10kA | 10kA | 10kA | 10kA | 50kA | 50kA | 50kA | 25kA |
| NB | 10 kA | B | - | - | - | - | 50kA | 50kA | 50kA | 25kA |
| NC | 10 kA | C | - | - | - | - | 50kA | 50kA | 50kA | 25kA |
| ND | 10 kA | D | - | - | - | - | 50kA | 50kA | 50kA | 25kA |