

Selectiviteitstabel: Smeltveiligheid en aardlekautomaten

Icc (kA)		Smeltveiligheden type gg NH														
IEC60898-1	In	16A	20A	25A	32A	35A	40A	50A	63A	80A	100A	125A	160A	200A	224A	250A
RCBO 4PP ADM4xxx	6A	0.20	0.30	0.50	1.10	1.30	1.60	2.60	3.00	5.90	T	T	T	T	T	T
	10A	0.20	0.30	0.50	1.00	1.20	1.40	2.30	2.70	5.30	T	T	T	T	T	T
	13A	0.20	0.30	0.50	1.00	1.10	1.40	2.10	2.40	4.20	T	T	T	T	T	T
	16A	-	-	0.50	0.90	1.00	1.30	1.90	2.10	3.80	T	T	T	T	T	T
	20A	-	-	-	0.90	1.00	1.20	1.70	1.90	3.20	5.00	T	T	T	T	T
	25A	-	-	-	0.90	1.00	1.20	1.70	1.90	3.10	4.80	T	T	T	T	T
	32A	-	-	-	-	-	-	1.50	1.70	2.80	4.40	T	T	T	T	T
	40A	-	-	-	-	-	-	-	1.70	2.70	4.20	6.00	T	T	T	T
B curve																
RCBO 4PP ADM4xxx	6A	0.30	0.40	0.50	1.10	1.30	1.60	2.50	3.00	5.80	T	T	T	T	T	T
	10A	-	0.40	0.50	1.00	1.20	1.40	2.20	2.60	5.00	T	T	T	T	T	T
	13A	-	-	0.50	1.00	1.10	1.30	2.00	2.30	4.40	T	T	T	T	T	T
	16A	-	-	-	0.90	1.00	1.30	1.80	2.10	3.50	5.70	T	T	T	T	T
	20A	-	-	-	-	-	1.20	1.70	2.00	3.40	5.40	T	T	T	T	T
	25A	-	-	-	-	0.90	1.10	1.60	1.80	3.20	5.20	T	T	T	T	T
	32A	-	-	-	-	-	-	-	1.70	2.80	4.60	T	T	T	T	T
	40A	-	-	-	-	-	-	-	-	2.40	4.00	5.90	T	T	T	T
C curve																

Icc (kA)		Smeltveiligheden type gg NH														
IEC60898-1	In	16A	20A	25A	32A	35A	40A	50A	63A	80A	100A	125A	160A	200A	224A	250A
RCBO	6A	0.20	0.50	0.90	2.50	3.00	4.00	T	T	T	T	T	T	T	T	T
	10A	0.20	0.30	0.60	1.60	1.90	2.40	3.90	4.70	T	T	T	T	T	T	T
	13A	-	0.30	0.60	1.50	1.80	2.30	3.60	4.20	T	T	T	T	T	T	T
	16A	-	-	0.50	1.30	1.50	1.90	2.90	3.30	T	T	T	T	T	T	T
	20A	-	-	-	1.10	1.30	1.70	2.60	3.00	5.70	T	T	T	T	T	T
	25A	-	-	-	-	1.20	1.50	2.30	2.70	5.00	T	T	T	T	T	T
	32A	-	-	-	-	-	-	2.10	2.40	4.30	T	T	T	T	T	T
	40A	-	-	-	-	-	-	-	2.30	4.10	T	T	T	T	T	T
B curve																
RCBO	6A	0.60	0.90	1.20	2.40	2.80	3.80	T	T	T	T	T	T	T	T	T
	10A	-	0.80	1.00	1.50	1.60	2.10	3.40	4.10	T	T	T	T	T	T	T
	13A	-	-	-	1.40	1.60	2.00	3.20	3.90	T	T	T	T	T	T	T
	16A	-	-	-	1.40	1.50	1.90	3.00	3.60	T	T	T	T	T	T	T
	20A	-	-	-	-	-	1.50	2.30	2.60	5.00	T	T	T	T	T	T
	25A	-	-	-	-	-	-	2.10	2.40	4.60	T	T	T	T	T	T
	32A	-	-	-	-	-	-	-	-	4.10	T	T	T	T	T	T
	40A	-	-	-	-	-	-	-	-	3.80	T	T	T	T	T	T
C curve																