

Description	Cat ref. Plain Door	Cat ref. Glazed Door
-------------	------------------------	-------------------------

Hybrid 250A Distribution Boards
Supplied with 250A 3P Switch Disconnecter Incomer Pre-Fitted

250A 2+10 Way Hybrid TPN Board	JK20210BSD	JK20210BGSD
250A 2+16 Way Hybrid TPN Board	JK20216BSD	JK20216BGSD
250A 2+20 Way Hybrid TPN Board	JK20220BSD	JK20220BGSD

Hybrid 250A TPN Distribution Boards Without Incomer Supplied

250A 2+10 Way Hybrid TPN Board	JK20210B	JK20210BG
250A 2+16 Way Hybrid TPN Board	JK20216B	JK20216BG
250A 2+20 Way Hybrid TPN Board	JK20220B	JK20220BG

Incomer Kits for 250A Boards

	Cat ref.
3 Pole 250A MCCB Incomer Kit (Fits within distribution board)	JK22503M
4 Pole 250A MCCB Incomer Kit (Fits within distribution board)	JK22504M
3 Pole 250A Switch Disconnecter Incomer Kit (Fits within distribution board)	JK22503S
4 Pole 250A Switch Disconnecter Incomer Kit (Fits within distribution board)	JK22504MCS
4 Pole 250A Direct Connection Kit (Fits within distribution board)	JK22504D
4 Pole 160A Contactor Incomer Kit includes Switch Disconnecter (Fits below distribution board, 450mm high)	JK21604C
3 Pole 125A MCCB Incomer Kit (Fits within distribution board)	JK21253M
4 Pole 125A MCCB Incomer Kit (Fits within distribution board)	JK21254M



Hager Ltd.
Hortonwood 50
Telford
Shropshire
TF1 7FT

Customer Contact Centre: 01952 675612
Technical Helpline: 01952 675689

hager.com/uk
sales@hager.co.uk
technical@hager.co.uk

- WhatsApp Tech Support: 07778 161000
- @HagerUK
- @HagerUK
- Hager UK
- @HagerukTV
- @Hager_uk

At A Glance

Invicta 3 Hybrid




Invicta 3 Hybrid Board
December 2020

To accommodate a variety of applications, we have a range of devices for protection metering and monitoring.



Aesthetics

The glazed door gives great aesthetics, especially in applications where the distribution board may be sited in public areas. This also allows unskilled people to check the status of devices through a locked door.



Flexibility

Two 3 phase loads of up to 125A or six single phase loads can be served from this TP&N Board with 27mm miniature circuit breakers. In the correct application this can replace the need for a separate MCCB panelboard.




Adaptable

Standard MCBs & RCBOs, meter packs and other common accessories are available from our 250A TP&N board range, giving you the same installation experience across the range.



Safety

The larger 80-125A MCB devices, whilst providing short circuit and overload protection, also give a disconnection point for downstream circuits (Isolation). This ensures that there are no unprotected outgoing connections from the busbar system.



Simple

Included as standard are larger Earth and Neutral connection points for larger cables.