

Sollysta 20A Double Pole Switch with Isolation Function

Industry first 20A Double Pole Switch with Isolation Function compliant with BS EN 60669-2-4.

Hager's Sollysta range uniquely offers a 20 Amp switch compliant with **BS EN 60669-2-4**, meaning it is certified as an isolation device as identified in Table 537.4 of the wiring regulations, BS 7671.

Hager are first to market with a 20A double pole switch with isolation function independently certified to BS EN 60669-2-4. The current edition of the wiring regulations, BS 7671, requires that devices used for isolation shall be of the type for which the isolation function is explicitly recognised by the relevant product standard.

Hager Sollysta allows electricians to choose the switch appropriate to the required function by offering both functional and isolation 20A double pole switch options.

The Sollysta 20A DP Switch with Isolation function will be available across most of the Sollysta range: Moulded, Decorative and Metalclad.



WMDP84NI




Description	Cat ref.
Moulded	
20A Double Pole Switch Isolation Function	WMDP84I
20A Double Pole Switch Isolation Function & Flex Outlet	WMDP84FOI
20A Double Pole Switch Isolation Function & LED Indicator	WMDP84NI
20A Double Pole Switch Isolation Function & LED Indicator & Flex Outlet	WMDP84FONI
20A Double Pole Switch Isolation Function & LED Indicator, Grey Plate	WMDP84NGI
20A Double Pole Switch Isolation Function LED & Flex Outlet, Print WATER HEATER	WMDP85FONI
20A Double Pole Switch Isolation & LED Indicator, Printed WATER HEATER	WMDP85NI
Metalclad	
20A Double Pole Switch Isolation Function LED Indicator & Flex Outlet Metalclad	WPDP84FONI
Decorative	
20A Double Pole Switch Isolation Function Black Nickel Black Insert	WRDP84NIBNB
20A Double Pole Switch Isolation Function Brushed Steel Black Insert	WRDP84NIBSB
20A Double Pole Switch Isolation Function Brushed Steel White Insert	WRDP84NIBSW
20A Double Pole Switch Isolation Function Polished Steel Black Insert	WRDP84NIPSB
20A Double Pole Switch Isolation Function Polished Steel White Insert	WRDP84NIPSW

Technical characteristics

Standard	BS EN 60669-2-4
Nominal voltage rating	250V AC
Current rating	20A
Fixing mode	Screws M3.5 x 30mm (included)
Material	Urea-formaldehyde / Stainless Steel
IP Protection Index	IP20

Warranty - Hager undertakes to replace or repair at its discretion products should they become inoperable within the time periods as stated.



A (mm)	B (mm)	C (mm)	D (mm)
86	86	30.2	17.3

Drawing based on WMDP84I