

Selectiviteitstabel: H3+ en installatieautomaten

Icc (kA)		H3+ P160 25/40/50/70kA TM												H3+ P250 25/40/50/70kA TM												H3+ P160 25/40/50/70kA Energy + LSI			H3+ P250 25/40/50/70kA Energy + LSI			H3 H1000 50/70kA LSI				H3 H1600 50/70kA LSI		
IEC60947-2	In	16	20	25	32	40	50	63	80	100	125	160	50	63	100	125	150	160	175	200	225	250	40	100	160	40	100	160	250	630	700	800	1000	800	1250	1600		
NBN B curve 10/15kA	6A	1.20	1.63	2.22	3.13	4.26	5.81	7.92	T	T	T	T	2.71	3.45	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
	10A	1.11	1.52	2.07	2.91	3.97	5.41	7.35	T	T	T	T	2.56	3.26	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
	13A	1.04	1.43	1.95	2.74	3.74	5.11	6.96	9.46	T	T	T	2.45	3.12	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
	16A	-	1.34	1.83	2.59	3.54	4.83	6.61	8.97	T	T	T	2.35	2.99	9.94	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
	20A	-	-	1.70	2.40	3.27	4.46	6.13	8.38	T	T	T	2.23	2.83	9.30	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
	25A	-	-	-	2.24	3.04	4.13	5.68	7.73	T	T	T	2.11	2.68	8.56	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
	32A	-	-	-	-	2.74	3.73	5.14	7.03	9.30	9.30	T	1.95	2.47	7.77	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
	40A	-	-	-	-	-	3.33	4.57	6.32	8.36	8.36	9.06	1.79	2.28	6.99	9.24	T	T	T	T	T	T	-	T	T	-	T	T	T	T	T	T	T	T	T	T	T	
	50A	-	-	-	-	-	-	4.01	5.57	7.42	7.42	8.04	-	2.06	6.20	8.19	T	T	T	T	T	T	-	T	T	-	T	T	T	T	T	T	T	T	T	T	T	T
63A	-	-	-	-	-	-	-	4.78	6.45	6.45	6.99	-	-	5.34	7.13	8.94	9.68	T	T	T	T	-	T	T	-	T	T	T	T	T	T	T	T	T	T	T	T	
NKN NCN C curve 10/15kA	0,5A	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
	1A	0.61	6.26	T	T	T	T	T	T	T	T	T	10.70	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
	2A	-	1.50	8.16	T	T	T	T	T	T	T	T	6.80	13.70	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
	3A	-	-	0.90	3.43	8.22	T	T	T	T	T	T	2.36	4.07	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
	4A	-	-	0.79	2.88	7.43	14.70	T	T	T	T	T	2.20	3.76	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
	6A	-	-	-	0.81	1.78	3.89	7.47	12.60	T	T	T	1.16	1.80	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
	10A	-	-	-	0.67	1.34	2.69	5.53	9.18	T	T	T	1.01	1.53	11.00	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
	13A	-	-	-	0.60	1.02	1.74	3.02	5.35	8.31	8.31	9.37	0.89	1.26	6.37	9.65	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
	16A	-	-	-	0.58	0.97	1.63	2.79	4.87	7.76	7.76	8.79	0.86	1.22	5.86	9.06	14.20	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
	20A	-	-	-	0.56	0.91	1.50	2.50	4.25	6.80	6.80	7.65	0.83	1.16	5.08	7.87	11.30	13.20	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T
	25A	-	-	-	0.54	0.88	1.44	2.39	4.05	6.48	6.48	7.25	0.81	1.13	4.83	7.45	10.30	11.80	14.30	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T
	32A	-	-	-	-	0.84	1.37	2.26	3.80	6.12	6.12	6.79	0.79	1.10	4.52	6.96	9.34	10.50	12.80	14.30	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T
	40A	-	-	-	-	-	1.31	2.13	3.50	5.56	5.56	6.29	0.78	1.08	4.13	6.46	8.77	9.78	11.70	13.10	14.00	14.30	-	T	T	-	T	T	T	T	T	T	T	T	T	T	T	T
	50A	-	-	-	-	-	-	1.99	3.23	5.07	5.07	5.78	-	1.04	3.80	5.96	7.86	8.66	9.90	10.80	11.30	11.50	-	T	T	-	T	T	T	T	T	T	T	T	T	T	T	T
	63A	-	-	-	-	-	-	-	3.11	4.85	4.85	5.51	-	-	3.65	5.68	7.54	8.29	9.45	10.30	10.80	11.00	-	T	T	-	T	T	T	T	T	T	T	T	T	T	T	T
NDN D curve 10/15kA	0,5A	T	12	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
	1A	-	2.94	T	T	T	T	T	T	T	T	T	6.22	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
	2A	-	1.41	9.75	12	T	T	T	T	T	T	T	5.25	11	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
	3A	-	-	0.84	3.54	8.47	T	T	T	T	T	T	1.70	2.69	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
	4A	-	-	0.66	2.58	7.29	11	13	T	T	T	T	1.57	2.49	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
	6A	-	-	-	0.70	1.61	3.69	7.40	13	T	T	T	1.11	1.59	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
	10A	-	-	-	0.63	1.25	2.47	5.00	8.48	13	13	14	1.05	1.48	9.90	14	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
	13A	-	-	-	0.56	0.95	1.62	2.81	4.96	7.83	7.83	8.83	0.95	1.32	6.00	9.09	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
	16A	-	-	-	0.56	0.95	1.62	2.81	4.96	7.83	7.83	8.83	0.93	1.30	6.00	9.09	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
	20A	-	-	-	0.54	0.89	1.47	2.47	4.24	6.74	6.74	7.52	0.89	1.23	5.07	7.72	12	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
	25A	-	-	-	0.52	0.85	1.39	2.32	3.93	6.32	6.32	7.05	0.86	1.18	4.68	7.24	9.86	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
	32A	-	-	-	-	0.83	1.34	2.18	3.62	5.82	5.82	6.52	0.83	1.13	4.30	6.68	9.03	13	14	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
	40A	-	-	-	-	-	1.26	2.04	3.33	5.28	5.28	6.02	0.81	1.10	3.93	6.18	8.32	9.25	11	T	T	-	T	T	-	T	T	T	T	T	T	T	T	T	T	T	T	
	50A	-	-	-	-	-	-	1.94	3.11	4.85	4.85	5.51	-	1.06	3.65	5.68	7.54	8.29	9.45	12	T	T	-	T	T	-	T	T	T	T	T	T	T	T	T	T	T	
	63A	-	-	-	-	-	-	-	2.93	4.49	4.49	5.08	-	-	3.41	5.24	7.07	7.77	8.86	9.58	13	T	-	T	-	T	T	-	T	T	T	T	T	T	T	T	T	T
HMB, HMC B, C curve 15/15kA	80A	-	-	-	-	-	-	-	-	3.29	3.29	3.65	-	-	2.61	3.74	5.03	5.58	6.45	7.03	7.39	7.51	-	-	T	-	T	T	T	T	T	T	T	T	T	T	T	T
	100A	-	-	-	-	-	-	-	-	3.29	3.65	-	-	-	3.74	5.03	5.58	6.45	7.03	7.39	7.51	-	-	-	T	-	-	T	T	T	T	T	T	T	T	T	T	
	125A	-	-	-	-	-	-	-	-	-	-	3.65	-	-	-	5.03	5.58	6.45	7.03	7.39	7.51	-	-	-	T	-	-	-	T	T	T	T	T	T	T	T	T	
	80A	-	-	-	-	-	-	-	-	3.25	3.25	3.52	-	-	2.71	3.59	4.52	4.90	5.48	5.86	6.15	6.27	-	-	T	-	T	T	T	T	T	T	T	T	T	T	T	
	100A	-	-	-	-	-	-	-	-	-	-	-	-	-	-	4.52	4.90	5.48	5.86	6.15	6.27	-	-	-	T	-	-	-	T	T	T	T	T	T	T	T	T	
15/15kA	125A	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	5.48	5.86	6.15	6.27	-	-	-	T	-	-	-	T	T	T	T	T	T	T	T	T	